

Cross reference list: DU / NO-DU variants

DU Material no.	DU Material description	NON-DU Material no.	NON-DU Material description
103047179	AZ201CC-T-1P2P-DU	103015814	AZ201CC-T-1P2P
103046784	AZ201ST2-T-1P2P-DU	103015816	AZ201ST2-T-1P2P
103047185	AZM201B-I2-CC-T-1P2PW-DU	103013488	AZM201B-I2-CC-T-1P2PW
103048758	AZM201B-I2-SK-T-1P2PW-A-DU	103013491	AZM201B-I2-SK-T-1P2PW-A
103044815	AZM201B-SK-T-1P2PW-A-DU	103013911	AZM201B-SK-T-1P2PW-A
103044809	AZM201B-SK-T-1P2PW-DU	103013910	AZM201B-SK-T-1P2PW
103046730	AZM201B-ST2-T-1P2PW-A-DU	103031956	AZM201B-ST2-T-1P2PW-A
103047904	AZM201B-ST-T-AS-P-DU	103025859	AZM201B-ST-T-AS-P
103045888	AZM201BZ-I2-ST-T-AS-P-DU	103025874	AZM201BZ-I2-ST-T-AS-P
103044816	AZM201BZ-ST-T-AS-P-DU	103025873	AZM201BZ-ST-T-AS-P
103046770	AZM201D-ST-T-1P2P2P-2965-1-DU	103042149	AZM201D-ST-T-1P2P2P-2965-1
103047181	AZM201Z-CC-T-1P2P-A-DU	103035307	AZM201Z-CC-T-1P2P-A
103047180	AZM201Z-CC-T-1P2P-DU	103027982	AZM201Z-CC-T-1P2P
103046786	AZM201Z-CC-T-1P2PW-2719-1-DU	103032190	AZM201Z-CC-T-1P2PW-2719-1
103047535	AZM201Z-CC-T-1P2PW-DU	103013912	AZM201Z-CC-T-1P2PW
103047182	AZM201Z-I2-CC-T-1P2P-DU	103033222	AZM201Z-I2-CC-T-1P2P
103046271	AZM201Z-I2-SK-T-1P2PW-A-DU	103016780	AZM201Z-I2-SK-T-1P2PW-A
103044814	AZM201Z-I2-SK-T-1P2PW-DU	103013484	AZM201Z-I2-SK-T-1P2PW
103044808	AZM201Z-I2-ST2-T-1P2PW-DU	103013486	AZM201Z-I2-ST2-T-1P2PW
103046565	AZM201Z-I2-ST2-T-SD2P-A-DU	103035058	AZM201Z-I2-ST2-T-SD2P-A
103045502	AZM201Z-I2-ST-T-AS-A-P-DU	103025863	AZM201Z-I2-ST-T-AS-A-P
103045503	AZM201Z-I2-ST-T-AS-P-DU	103025868	AZM201Z-I2-ST-T-AS-P
103044811	AZM201Z-SK-T-1P2PW-A-DU	103016752	AZM201Z-SK-T-1P2PW-A
103047366	AZM201Z-SK-T-SD2P-DU	103032241	AZM201Z-SK-T-SD2P
103046746	AZM201Z-ST2-T-1P2P-DU	103027308	AZM201Z-ST2-T-1P2P
103044813	AZM201Z-ST2-T-1P2PW-A-DU	103016753	AZM201Z-ST2-T-1P2PW-A
103046452	AZM201Z-ST2-T-SD2P-A-DU	103032732	AZM201Z-ST2-T-SD2P-A
103044810	AZM201Z-ST-T-1P2PW-2965-1-DU	103025499	AZM201Z-ST-T-1P2PW-2965-1
103047926	AZM201Z-ST-T-1P2PW-2965-2-DU	103025213	AZM201Z-ST-T-1P2PW-2965-2
103048454	AZM201Z-ST-T-1P2PW-2965-3-DU	103025497	AZM201Z-ST-T-1P2PW-2965-3
103047192	AZM201Z-ST-T-1P2PW-A-2965-1-DU	103025498	AZM201Z-ST-T-1P2PW-A-2965-1
103044798	AZM300B-I2-ST-1P2P-A-DU	103001427	AZM300B-I2-ST-1P2P-A
103044806	AZM300B-I2-ST-1P2P-A-T-DU	103010555	AZM300B-I2-ST-1P2P-A-T
103047072	AZM300B-I2-ST-1P2P-DU	103001415	AZM300B-I2-ST-1P2P
103047120	AZM300B-I2-ST-AS-A-DU	103005906	AZM300B-I2-ST-AS-A
103045604	AZM300B-I2-ST-AS-A-P-DU	103005904	AZM300B-I2-ST-AS-A-P
103047119	AZM300B-I2-ST-SD2P-A-T-DU	103012534	AZM300B-I2-ST-SD2P-A-T
103048501	AZM300B-ST-1P2P-A-DU	103001423	AZM300B-ST-1P2P-A
103044802	AZM300B-ST-1P2P-DU	103001411	AZM300B-ST-1P2P
103049631	AZM300B-ST-1P2P-T-DU	103006862	AZM300B-ST-1P2P-T
103047556	AZM300B-ST-SD2P-A-DU	103001424	AZM300B-ST-SD2P-A
103044801	AZM300Z-I2-ST-1P2P-A-DU	103001454	AZM300Z-I2-ST-1P2P-A
103044805	AZM300Z-I2-ST-1P2P-A-T-DU	103010774	AZM300Z-I2-ST-1P2P-A-T
103044800	AZM300Z-I2-ST-1P2P-DU	103001439	AZM300Z-I2-ST-1P2P
103046771	AZM300Z-I2-ST-1P2P-N-DU	103006868	AZM300Z-I2-ST-1P2P-N
103044799	AZM300Z-I2-ST-1P2P-T-DU	103006863	AZM300Z-I2-ST-1P2P-T
103045603	AZM300Z-I2-ST-AS-P-DU	103005918	AZM300Z-I2-ST-AS-P
103047344	AZM300Z-I2-ST-AS-T-DU	103011892	AZM300Z-I2-ST-AS-T
103047256	AZM300Z-I2-ST-SD2P-DU	103001440	AZM300Z-I2-ST-SD2P
103047748	AZM300Z-ST-1P2P-A-DU	103001450	AZM300Z-ST-1P2P-A
103045791	AZM300Z-ST-1P2P-DU	103001435	AZM300Z-ST-1P2P

Cross reference list: DU / NO-DU variants

DU Material no.	DU Material description	NON-DU Material no.	NON-DU Material description
103046632	AZM300Z-ST-1P2P-N-DU	103006869	AZM300Z-ST-1P2P-N
103049029	AZM300Z-ST-1P2P-T-DU	103006865	AZM300Z-ST-1P2P-T
103048005	AZM300Z-ST-SD2P-A-DU	103001451	AZM300Z-ST-SD2P-A
103046631	AZM300Z-ST-SD2P-T-DU	103008177	AZM300Z-ST-SD2P-T
103046589	AZM400Z-ST2-I2-2P2P-E-DU	103003725	AZM400Z-ST2-I2-2P2P-E
103048586	AZM400Z-ST-I2-1P2P-BOW-DU	103015315	AZM400Z-ST-I2-1P2P-BOW
103044780	AZM400Z-ST-I2-1P2P-DU	103003733	AZM400Z-ST-I2-1P2P
103046989	AZM400Z-ST-I2-1P2P-T-DU	103003841	AZM400Z-ST-I2-1P2P-T
103044785	AZM40B-I2-ST-1P2P-DU	103034195	AZM40B-I2-ST-1P2P
103044784	AZM40B-I2-ST-1P2P-PH-DU	103037332	AZM40B-I2-ST-1P2P-PH
103044782	AZM40Z-I2-ST-1P2P-DU	103034189	AZM40Z-I2-ST-1P2P
103044783	AZM40Z-I2-ST-1P2P-PH-DU	103037335	AZM40Z-I2-ST-1P2P-PH
103046813	EX-AZM300B-ST-1P2P-A-CL-3GD-DU	103012541	EX-AZM300B-ST-1P2P-A-CL-3GD
103046812	EX-AZM300B-ST-1P2P-A-CR-3GD-DU	103012540	EX-AZM300B-ST-1P2P-A-CR-3GD
103048511	EX-AZM300Z-I2-ST-1P2P-CL-3GD-DU	103039218	EX-AZM300Z-I2-ST-1P2P-CL-3GD
103048510	EX-AZM300Z-I2-ST-1P2P-CR-3GD-DU	103039219	EX-AZM300Z-I2-ST-1P2P-CR-3GD
103048529	EX-RSS16-I2-D-10M-3G/D-DU	103034308	EX-RSS16-I2-D-10M-3G/D
103047171	MZM 100 B ST2-1P2PW2R200M-A-DU	101210773	MZM 100 B ST2-1P2PW2R200M-A
103047170	MZM 100 B ST2-1P2PW2R60M-A-DU	101210772	MZM 100 B ST2-1P2PW2R60M-A
103048086	MZM 100 B ST2-1P2PW2R-A-DU	101206028	MZM 100 B ST2-1P2PW2R-A
103048084	MZM 100 B ST2-1P2PW2RE-A-DU	101211070	MZM 100 B ST2-1P2PW2RE-A
103044830	MZM 100 B ST2-1P2PW2REM-A-2930-DU	103013468	MZM 100 B ST2-1P2PW2REM-A-2930
103044828	MZM 100 B ST2-1P2PW2REM-A-DU	101211071	MZM 100 B ST2-1P2PW2REM-A
103046451	MZM 100 B ST2-SD2PREM-A-2930-DU	103014614	MZM 100 B ST2-SD2PREM-A-2930
103046571	MZM 100 B ST2-SD2PREM-A-DU	101211153	MZM 100 B ST2-SD2PREM-A
103044829	MZM 100 B ST-AS REMAP-DU	101209551	MZM 100 B ST-AS REMAP
103048089	MZM 100 ST-1P2PR-A-DU	101187450	MZM 100 ST-1P2PR-A
103047121	MZM 100 ST-1P2PW-A-DU	101199544	MZM 100 ST-1P2PW-A
103047169	MZM 100 ST-1P2PWR100-A-DU	101194473	MZM 100 ST-1P2PWR100-A
103047122	MZM 100 ST2-1P2P-A-DU	101199622	MZM 100 ST2-1P2P-A
103047123	MZM 100 ST2-1P2PR-A-DU	101210074	MZM 100 ST2-1P2PR-A
103045662	MZM 100 ST2-1P2PWM-A-3107-DU	101209059	MZM 100 ST2-1P2PWM-A
103048088	MZM 100 ST2-1P2PWRE-A-DU	101211066	MZM 100 ST2-1P2PWRE-A
103044831	MZM 100 ST2-1P2PWREM-A-DU	101211067	MZM 100 ST2-1P2PWREM-A
103046764	MZM 100 ST-AS REMAP-DU	101209553	MZM 100 ST-AS REMAP
103047214	RSS 36-AD-ST-AS-DU	103001535	RSS 36-AD-ST-AS
103044826	RSS 36-D-R-ST-DU	101213956	RSS 36-D-R-ST
103046834	RSS 36-D-ST-2685-1-DU	101217466	RSS 36-D-ST-2685-1
103046542	RSS 36-D-ST-DU	101213954	RSS 36-D-ST
103045606	RSS 36-I2-D-R-ST-DU	101214773	RSS 36-I2-D-R-ST
103044825	RSS 36-I2-D-ST-DU	101216956	RSS 36-I2-D-ST
103047213	RSS 36-I2-SD-ST-DU	101218833	RSS 36-I2-SD-ST
103046644	RSS 36-I2-ST-AS-DU	103001538	RSS 36-I2-ST-AS
103049145	RSS 36-SD-R-ST-DU	101217290	RSS 36-SD-R-ST
103044827	RSS 36-SD-ST-DU	101214772	RSS 36-SD-ST
103044778	RSS16-D-R-ST8H-DU	103004338	RSS16-D-R-ST8H
103044779	RSS16-D-SK-DU	103004343	RSS16-D-SK
103044777	RSS16-I2-D-CC-DU	103004351	RSS16-I2-D-CC
103044776	RSS16-I2-D-ST8H-DU	103004339	RSS16-I2-D-ST8H
103047323	RSS16-SD-ST8H-DU	103006685	RSS16-SD-ST8H